


# Parallel kit EAMM-U-60-D32-40G-91-S1

Part number: 1577346

FESTO

Suitable for electric drives.



## Data sheet

| Feature                  | Value                  |
|--------------------------|------------------------|
| Size                     | 60                     |
| Assembly position        | Any                    |
| Gear unit ratio          | 1:1                    |
| Max. speed               | 6,000 1/min            |
| PWIS conformity          | VDMA24364 zone III     |
| Storage temperature      | -25 ... 60 °C          |
| Relative air humidity    | 0 - 95 %               |
| Protection class         | IP65                   |
| Ambient temperature      | -10 ... 60 °C          |
| Mass moment of inertia   | 26.7 kgmm <sup>2</sup> |
| No-load driving torque   | 0.07 Nm                |
| Transferable torque      | 3 Nm                   |
| Product weight           | 1,140 g                |
| Interface code, actuator | D32B                   |
| Interface code, motor in | 40G                    |
| Materials note           | Conforms to RoHS       |