


# Suction cup VAS-55-1/4-SI

Part number: 158976

FESTO

Sealing ring is not included in the scope of delivery.  
Type to be discontinued. Available until 2013.



## Data sheet

Feature	Value
Nominal size	4 mm
suction cup diameter	55 mm
Effective suction diameter	44 mm
Design structure	Vacuum connection at top round, standard
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:-:-]
Ambient temperature	-40 ... 200 °C
Breakaway force at 70% vacuum	106 N
Product weight	16 g
Mounting thread	G1/4
suction cup mounting	G 1/4
Vacuum connection	G1/4
Shore hardness	60 +/- 5
Materials information for screw-in stud	Wrought Aluminum alloy
Materials note	Contains PWIS substances
Materials information for suction cup	VMQ (silicon)