


Connecting cable KMP1-02-VI-6-X

Part number: 158984
Product to be discontinued

FESTO

The cable is available in lengths from 1 to 99 m.

Type to be discontinued. Available until 2017. See Support Portal for alternative products.



Exemplary representation

Data sheet

Feature	Value
Assembly position	Any
Operating voltage range AC	≤ 300 V
Operating voltage range DC	≤ 250 V
Permissible current load	4 A
Protection class	IP65
Ambient temperature with flexible cable installation	5 ... 70 °C
Ambient temperature	-30 ... 70 °C
Electrical connection	25-pin Plug socket
Cable structure	13 x 0,75 mm ²
Cable diameter	10 mm
Mounting type	With clamp strap
Materials information, housing	Die-cast light alloy
Materials information, cable sheaths	PE
Material information for crimp connectors	Silver plated Copper alloy