

Compact cylinder ADVULQ-2"- -A-P-A

Part number: 160596



FESTO

For proximity sensing. Secured against rotation by means of square piston rod. Piston-rod end with male thread.

Nut for piston rod thread is included.

This product is only available if ordered from the Festo Corporation, USA.

Type to be discontinued. Available until 2011.



Data sheet

Feature	Value
Stroke	0.04 ... 12 "
Piston diameter	2"
Cushioning	P: Flexible cushioning rings/plates at both ends
Mode of operation	double-acting
Piston-rod end	Male thread
Protection against torque/guide	Square piston rod
Working pressure	11.6 ... 145 Psi
Operating medium	Filtered compressed air
Corrosion resistance classification CRC	2
Ambient temperature	-4 ... 176 °F
Theoretical force at 6 bar, return stroke	1,057 N
Theoretical force at 6 bar, advance stroke	1,178 N
Moving mass with 0 mm stroke	112 g
Additional weight per 10 mm stroke	16 g
Basic weight for 0 mm stroke	560 g
Pneumatic connection	NPT1/8-27
Working pressure [psi]	11.6 ... 145 psi
Materials information for cover	Wrought Aluminum alloy
Materials information for dynamic seals	TPE-U(PU) NBR
Materials information for piston rod	High alloy steel
Materials information for cylinder barrel	Wrought Aluminum alloy