

Compact cylinder

AEVU-1 5/8"- -P-A



Part number: 160605

FESTO

For proximity sensing, piston-rod end with female thread.

This product is only available if ordered from the Festo Corporation, USA.

Type to be discontinued. Available until 2011.



Data sheet

Feature	Value
Stroke	0.2 ... 1 "
Piston diameter	1 5/8"
Cushioning	P: Flexible cushioning rings/plates at both ends
Mode of operation	single-acting pushing action
Piston-rod end	Female thread
Working pressure	11.6 ... 145 Psi
Operating medium	Filtered compressed air
Corrosion resistance classification CRC	2
Ambient temperature	-4 ... 176 °F
Theoretical force at 6 bar, advance stroke	704 N
Moving mass with 0 mm stroke	63 g
Additional weight per 10 mm stroke	9 g
Basic weight for 0 mm stroke	433 g
Additional mass factor per 10 mm of stroke	23 g
Pneumatic connection	NPT1/8-27
Working pressure [psi]	11.6 ... 145 psi
Materials information for cover	Wrought Aluminum alloy
Materials information for dynamic seals	TPE-U(PU) NBR
Materials information for piston rod	High alloy steel
Materials information for cylinder barrel	Wrought Aluminum alloy