

Sealing ring OL-M12

Part number: 161182

FESTO

Leak-free



Data sheet

Feature	Value
Based on the standard	ISO 16030
Container size	1
Operating pressure complete temperature range	-0.95 ... 30 bar
Corrosion resistance classification CRC	2 - Moderate corrosion stress
Ambient temperature	-40 ... 100 °C
Manual tightening at ambient temperature	Yes
Nominal tightening torque	13.5 Nm
Tolerance for nominal tightening torque	± 20 %
Materials note	Conforms to RoHS