


Multi-position kit DPVU-40

Part number: 161198

FESTO

Allows assembly of 3- and 4-position cylinders, each consisting of 2 standard ADVU cylinders.



Data sheet

Feature	Value
Size	40
Corrosion resistance classification CRC	2 - Moderate corrosion stress
PWIS conformity	VDMA24364-B2-L
Ambient temperature	-40 ... 150 °C
Product weight	155 g
Materials note	Conforms to RoHS
Material flange	Wrought Aluminum alloy
Material screws	Steel Galvanized
Material cylindrical dowel pin	Steel Galvanized