

Push-in T-fitting CRQST-1/8-6

Part number: 164202

FESTO

360° orientable, male thread with external hexagon.



Data sheet

Feature	Value
Size	Standard
Nominal size	3.7 mm
Assembly position	Any
Design	T-shaped
Container size	1
Design structure	Push/pull principle
Operating pressure for entire temperature range	-0.095 ... 1 MPa
Operating pressure complete temperature range	-0.95 ... 10 bar
Operating pressure for entire temperature range	-13.775 ... 145 psi
Note on working pressure	Water: max. 0.6 MPa at max. 50°C
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:-:-] Water (liquid, free of ice)
Note on operating and pilot medium	Lubricated operation possible
Corrosion resistance classification CRC	4 - Very high corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Food-safe	See Supplementary material information
Ambient temperature	-15 ... 120 °C
Product weight	25 g
Number of outputs	2
Number of supply lines	1
Usable wires	PFAN
Mounting type	External hex A/F 12
Pneumatic connection, port 1	Male thread R1/8
Pneumatic connection, port 2	For tubing outside diameter 6 mm
Material of threaded plug	High alloy steel, non-corrosive
Materials note	Conforms to RoHS
Material housing	High alloy steel, non-corrosive
Material release ring	High alloy steel, non-corrosive
Material of tubing seal	FPM
Material of tube retaining claw	High alloy steel, non-corrosive
Thrust ring material	High alloy steel, non-corrosive