


# Stopper cylinder STAF-50-30-P-A-K

Part number: 164881

FESTO

With toggle lever and built-in flange plate.

This product may not be used within liquid media. Easy retrofitting to a double-acting cylinder is possible.



## Data sheet

Feature	Value
Stroke	30 mm
Piston diameter	50 mm
Cushioning	P: Flexible cushioning rings/plates at both ends
Assembly position	Vertical
Mode of operation	single-acting pulling action
Design structure	Piston rod with toggle lever
Position detection	For proximity sensor
Variants	Single-ended piston rod
Protection against torque/guide	Guide rod
Working pressure	1.5 ... 10 bar
Operating medium	Filtered compressed air
Corrosion resistance classification CRC	2
Ambient temperature	5 ... 60 °C
Impact force	1,200 N
Product weight	1,810 g
Mounting type	with through hole
Pneumatic connection	G1/8
Materials note	Free of copper and PTFE
Materials information for cover	Aluminum
Materials information for seals	NBR
Materials information, housing	Aluminum
Materials information for piston rod	High alloy steel, non-corrosive