


Transmitter SOEG-S-Q30-S-L

Part number: 165353
Product to be discontinued

FESTO

Type to be discontinued. Available until 2020. See Support Portal for alternative products.



Data sheet

Feature	Value
Conforms to standard	EN 60947-5-2
Authorization	RCM Mark c UL us - Listed (OL)
CE symbol (see declaration of conformity)	according to EU-EMV guideline
Materials note	Free of copper and PTFE
Measurement method	Through-beam sensor Transmitter
Type of light	Infrared
Ambient temperature	-25 ... 55 °C
Voltage drop	2 V
Operating voltage range DC	10 ... 30 V
Residual ripple	20 %
Idle current	25 mA
Polarity protected	for all electrical connections
Electrical connection	Plug M8x1 3-pin
Size	30x30x15 mm
Mounting type	with through hole
Product weight	18 g
Material housing	PBT-reinforced
Upper limit of adjustment range	6 mm
Ambient temperature with flexible cable installation	-5 ... 55 °C
Protection class	IP65
Corrosion resistance classification CRC	2 - Moderate corrosion stress