

Fibre-optic cable SOEZ-LLG-SE-0,5-M4

Part number: 165357

FESTO



Data sheet

Feature	Value
Measurement method	Through-beam sensor Fiber optics
Ambient temperature	-20 ... 160 °C
Size	M4
Product weight	46 g
Material housing	Brass Chromed-plated
Upper limit of adjustment range	280 mm
Ambient temperature of flexible installation	-20 ... 120 °C
Protection class	IP54
PWIS conformity	VDMA24364-B2-L