



Branching module FRM-H-D-MIDI

Part number: 170688
Classic - do not use for new projects

FESTO

Pneumatic manifold with 4 connections, attachment facility for auxiliary modules, without threaded connection plates with FRB threaded pin.

Modern alternatives can be found by entering the first four characters of the type code in the search field.



Data sheet

Feature	Value
Assembly position	Any
Design structure	Branching module
Working pressure	0.2 ... 16 bar
Standard nominal flow rate in main flow direction 1->2	5,100 l/min
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:-:-] Inert gases
Corrosion resistance classification CRC	2 - Moderate corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Storage temperature	-10 ... 60 °C
Air purity class at output	Compressed air in accordance with ISO8573-1:2010 [7:-:-] Inert gases
Medium temperature	-10 ... 60 °C
Ambient temperature	-10 ... 60 °C
Product weight	386 g
Pneumatic connection, port 3	G1/2
Pneumatic connection, port 4	G1/4
Materials note	Conforms to RoHS
Material housing	Aluminum die cast