

Suction cup VAS-10-M5-PUR

Part number: 173441

FESTO

With sealing ring OL.



Data sheet

Feature	Value
Nominal size	2 mm
suction cup diameter	10 mm
Effective suction diameter	8 mm
Design structure	Vacuum connection at top round, standard
Operating medium	Atmospheric air
Ambient temperature	-20 ... 60 °C
Breakaway force at 70% vacuum	4.5 N
Mounting thread	M5
suction cup mounting	M5
Vacuum connection	M5
Shore hardness	62
Materials information for screw-in stud	Brass
Materials information for suction cup	TPE-U(PU)