

Fine filter combination LFMBA-1-D-MAXI-NPT


Part number: 173754

Classic - do not use for new projects

Micro filter 1 µm for prefiltration and micro filter 0.01 µm, with metal bowl guard.

Modern alternatives can be found by entering the first four characters of the type code in the search field.

FESTO



Data sheet

Feature	Value
Size	Maxi
Series	D
Assembly position	Vertical
Grade of filtration	0.01 µm
Filter efficiency	99.9999 %
Condensate drain	manual momentary-contact
Bowl guard	Metal bowl guard
Working pressure	1 ... 16 bar
Operating medium	Compressed air in accordance with ISO8573-1:2010 [6:8:4] Inert gases
PWIS conformity	VDMA24364-B1/B2-L
Air purity class at output	Compressed air in accordance with ISO8573-1:2010 [1:7:2] Inert gases
Medium temperature	1.5 ... 60 °C
Residual oil content	0.01 mg/m ³
Ambient temperature	-10 ... 60 °C
Mounting type	Line installation with accessories
Pneumatic connection, port 1	1 NPT
Pneumatic connection, port 2	1 NPT
Materials note	Conforms to RoHS
Material filter	Boron silicate fiber
Material housing	Zinc die-casting
Material bowl	PC