

Service unit FRC-3/4-D-MAXI-NPT

Part number: 173876

Classic - do not use for new projects

FESTO

Filter/regulator/lubricator combination, 40 µm filter, with metal bowl guard. With manual condensate drain.

Modern alternatives can be found by entering the first four characters of the type code in the search field.



Data sheet

| Feature | Value |
|---|---|
| Size | Maxi |
| Assembly position | Vertical |
| Condensate drain | manual rotary |
| Grade of filtration | 40 µm |
| Working pressure | 1 ... 16 bar |
| Standard nominal flow rate | 8,300 l/min |
| Operating medium | Compressed air to ISO 8573-1:2010 [-:9:-] Inert gases |
| Note on operating and pilot medium | Lubricated operation possible (subsequently required for further operation) |
| Corrosion resistance classification CRC | 2 - Moderate corrosion stress |
| PWIS conformity | VDMA24364-B1/B2-L |
| Air purity class at output | Compressed air to ISO 8573-1:2010 [7:8:-] Inert gases |
| Medium temperature | -10 ... 60 °C |
| Ambient temperature | -10 ... 60 °C |
| Product weight | 2,390 g |
| Mounting type | Line installation With mounting bracket Optional |
| Pneumatic connection, port 1 | 3/4 NPT |
| Pneumatic connection, port 2 | 3/4 NPT |
| Materials note | Conforms to RoHS |
| Material housing | Zinc die-casting |
| Material bowl | PC |