


# Coupling EAMC-65-90-XX-25

Part number: 176038

FESTO

For DGE.



## Data sheet

Feature	Value
Holder diameter 2	25 mm
Size	65
Nominal length	90 mm
Assembly position	Any
Max. speed	4,500 1/min
PWIS conformity	VDMA24364-B2-L
Storage temperature	-25 ... 60 °C
Relative air humidity	0 - 95 %
Ambient temperature	-25 ... 60 °C
Mass moment of inertia	417 kgmm <sup>2</sup>
Product weight	535 g
Materials note	Conforms to RoHS