



Round cylinder DSAQ-25- -PPV-A-Q

Part number: 176376

FESTO

End cap with air connection perpendicular to cylinder axis, with square piston rod

This product is only available if ordered from Festo Korea Co. Ltd.



Exemplary representation

Data sheet

| Feature | Value |
|--|---|
| Stroke | 1 ... 500 mm |
| Piston diameter | 25 mm |
| Cushioning | PPV: Pneumatic cushioning adjustable at both ends |
| Protection against torque/guide | Square guide |
| Working pressure | 1 ... 10 bar |
| Mode of operation | double-acting |
| Operating medium | Compressed air in accordance with ISO8573-1:2010 [7:4:4] |
| Note on operating and pilot medium | Lubricated operation possible (subsequently required for further operation) |
| Corrosion resistance classification CRC | 2 |
| Ambient temperature | -20 ... 80 °C |
| Cushioning length | 17 mm |
| Theoretical force at 6 bar, return stroke | 247.4 N |
| Theoretical force at 6 bar, advance stroke | 294.5 N |
| Moving mass with 0 mm stroke | 141 g |
| Additional weight per 10 mm stroke | 11.1 g |
| Basic weight for 0 mm stroke | 212 g |
| Additional mass factor per 10 mm of stroke | 6.2 g |
| Pneumatic connection | M26x1,5 |
| Materials information for cover | Wrought Aluminum alloy |
| Materials information for seals | NBR TPE-U(PU) |
| Materials information, housing | High alloy steel, non-corrosive |
| Materials information for piston rod | High alloy steel, non-corrosive |