

Valve manifold

VIMP-04-D-1


Part number: 18084

FESTO

with multi-pin connection, size 1.

Depending on the configuration, the illustrations, the technical data on the data sheet and the relevant accessories might not exactly match this product.

Type to be discontinued. Available until 2011.



Data sheet

~ConfIndependentDatasheet

Feature	Value
Valve function	5/2 monostable 5/2 bistable 5/3 pressurized 5/3 exhausted 5/3 closed
Standard nominal flow rate	1,200 ... 2,600 l/min
Working pressure	-0.9 ... 10 bar
Electrical connection	Multipol
Max. number of valve positions	14
Ambient temperature	-10 ... 60 °C
Protection class	IP65
Exhaust-air function	throttleable
Type of actuation	electrical
Valve manifold type	04
Design structure	Piston slide
Pilot air supply	external Internal
Valve manifold structure	modular and expandable
Switching position indicator	LED
Pilot pressure	2 ... 10 bar
Suitability for vacuum	Yes
Nominal operating voltage, AC	110 V
Nominal operating voltage DC	24 V
CE symbol (see declaration of conformity)	according to EU low voltage guideline
Medium temperature	-10 ... 60 °C