


Electrical module CP-A08N-M12

Part number: 18234

FESTO

For valve manifold



Data sheet

Feature	Value
ATEX category Gas	II 3G
Explosion ignition protection type Gas	Ex nA IIC T5 X Gc
ATEX category Dust	II 3D
Explosion ignition protection type Dust	Ex tc IIIC T80°C X Dc IP65
Explosion-proof ambient temperature	-5 °C ≤ Ta ≤ +50 °C
CE symbol (see declaration of conformity)	according to EU-EMV guideline according to EU-Ex protection guideline (ATEX)
Authorization	c UL us - Recognized (OL)