


Suction cup VAS-15-1/8-PUR-CT

Part number: 183512

FESTO

With sealing ring OL.
Run-out type. Available until 2010.



Data sheet

Feature	Value
Nominal size	3 mm
suction cup diameter	15 mm
Effective suction diameter	12 mm
Design structure	Vacuum connection at top round, standard
Operating medium	Atmospheric air
Ambient temperature	-20 ... 60 °C
Breakaway force at 70% vacuum	7.9 N
Mounting thread	G1/8
suction cup mounting	G 1/8
Vacuum connection	G1/8
Shore hardness	62
Materials information for screw-in stud	High alloy steel, non-corrosive
Materials note	Free of copper and PTFE
Materials information for suction cup	TPE-U(PU)