

Bellows suction cup VASB-30-1/8-NBR-CT

Part number: 183516

FESTO

With sealing ring OL.
Run-out type. Available until 2010.



Data sheet

Feature	Value
Nominal size	3 mm
suction cup diameter	30 mm
Effective suction diameter	25 mm
Design structure	Vacuum connection at top round, bellows 1.5 convolutions
Operating medium	Atmospheric air
Ambient temperature	-20 ... 80 °C
Breakaway force at 70% vacuum	34 N
Mounting thread	G1/8
suction cup mounting	G 1/8
Vacuum connection	G1/8
Shore hardness	73
Materials note	Free of copper and PTFE
Materials information for suction cup	TPE-U(PU)