


Vacuum gauge

VAM-63-V1/0-1/4-CT

Part number: 183522

FESTO

With display unit in bar and psi.
Run-out type. Available until 2010.



Data sheet

Feature	Value
Nominal size of pressure gauge	63
Position of connection	Rear side central
Based on the standard	DIN EN 837-1
Type of seal on screw-in stud	coating
Assembly position	Any
Conforms to standard	DIN EN 837-1
Design structure	Bourdon-tube pressure gauge
Indicating range [bar]	-1 ... 0 bar
Indicating range [psi]	-14.5 ... 0 psi
Scale	Double scale Bar (external) Inch hg (inside) / psi (inside)
Working pressure	-1 ... 0 bar
Operating medium	Dried, filtered and lubricated compressed air Vacuum
Continuous load factor	0.75
Alternating load factor	0.66
Corrosion resistance classification CRC	4
Medium temperature	-20 ... 60 °C
Protection class	IP43
Ambient temperature	-40 ... 60 °C
Product weight	112 g
Measurement accuracy class	2,5
Mounting type	Threaded
Pneumatic connection	G1/4
Materials information for screw-in stud	High alloy steel, non-corrosive
Materials note	Free of copper and PTFE
Materials information, housing	High alloy steel, non-corrosive
Materials info, viewing window	PC