

Compact cylinder

ADVU-5"- -P-A


Part number: 183630

FESTO


For proximity sensing, piston-rod end with female thread.

This product is only available if ordered from the Festo Corporation, USA.

Type to be discontinued. Available until 2011.



Exemplary representation



Data sheet

Feature	Value
Stroke	0.04 ... 16 "
Piston diameter	5"
Cushioning	P: Flexible cushioning rings/plates at both ends
Mode of operation	double-acting
Piston-rod end	Female thread
Working pressure	7.3 ... 145 Psi
Operating medium	Filtered compressed air
Corrosion resistance classification CRC	2
Ambient temperature	-4 ... 176 °F
Theoretical force at 6 bar, return stroke	6,881 N
Theoretical force at 6 bar, advance stroke	7,363 N
Moving mass with 0 mm stroke	1,317 g
Additional weight per 10 mm stroke	63 g
Basic weight for 0 mm stroke	3,426 g
Additional mass factor per 10 mm of stroke	59 g
Pneumatic connection	NPT1/4-18
Working pressure [psi]	7.3 ... 145 psi
Materials information for cover	Wrought Aluminum alloy
Materials information for dynamic seals	TPE-U(PU) NBR
Materials information for piston rod	High alloy steel
Materials information for cylinder barrel	Wrought Aluminum alloy