

# Pressure gauge MA-40-1,6-G1/4-MPA

Part number: 184287  
Product to be discontinued

With display unit in MPa.

Type to be discontinued. Available until 2014. See Support Portal for alternative products.

FESTO



## Data sheet

Feature	Value
Indicating range [MPa]	0 ... 1.6 MPa
Conforms to standard	EN 837-1
Nominal size of pressure gauge	40
Design structure	Bourdon-tube pressure gauge
Mounting type	Line installation
Operating medium	Inert gases Neutral fluids
Working pressure	0 ... 1.6 MPa
Alternating load factor	0.66
Measurement accuracy class	2,5
Protection class	IP43
Medium temperature	-20 ... 60 °C
Ambient temperature	-20 ... 60 °C
Materials note	Conforms to RoHS
Position of connection	Rear side central
Pneumatic connection	G1/4
Materials in contact with media	Brass
Materials information for screw-in stud	Brass
Materials information, housing	ABS
Materials info, viewing window	PS
Housing color	Black
Product weight	70 g
Note on operating and pilot medium	No oxygen No acetylene