

Valve manifold VIMP-02-1/8-4

Part number: 18562

FESTO

G1/8, with multi-pin connection.



Data sheet

Feature	Value
Valve function	5/2 single solenoid 5/2 bistable 5/3 pressurized 5/3 exhausted 5/3 closed
Standard nominal flow rate	750 ... 1,000 l/min
Working pressure	-0.9 ... 10 bar
Electrical connection	Multipol
Max. number of valve positions	4
Ambient temperature	-5 ... 50 °C
Protection class	IP65
Type of actuation	electrical
Valve manifold type	02
Design structure	Piston slide
Pilot air supply	external Internal
Valve manifold structure	Fixed-grid
Pilot pressure	1.5 ... 10 bar
Nominal operating voltage DC	24 V
Medium temperature	-5 ... 50 °C
Materials note	Contains PWIS substances