

Multiple distributor QSLV2-G1/8-4

Part number: 186223

FESTO

2-fold, 360° orientable.



Data sheet

Feature	Value
Size	Standard
Nominal size	2.4 mm
Type of seal on screw-in stud	Sealing ring
Assembly position	Any
Design structure	Push/pull principle
Container size	1
Operating pressure for entire temperature range	-0.095 ... 0.6 MPa
Operating pressure complete temperature range	-0.95 ... 6 bar
Operating pressure for entire temperature range	-13.775 ... 87 psi
Temperature-dependent operating pressure	-0.095 ... 1.4 MPa
Temperature dependent working pressure	-0.95 ... 14 bar
Temperature-dependent operating pressure	-13.775 ... 203 psi
Maritime classification	see certificate
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:-:] Water as per manufacturer's declaration at www.festo.com
Note on operating and pilot medium	Lubricated operation possible
Corrosion resistance classification CRC	1 - Low corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 ... 80 °C
Nominal tightening torque	7 Nm
Tolerance for nominal tightening torque	± 20 %
Product weight	25 g
Number of outputs	2
Number of supply lines	1
Pneumatic connection, port 1	Male thread G1/8
Pneumatic connection, port 2	For tubing outside diameter 4 mm
color of release ring	blue
Materials note	Conforms to RoHS
Material housing	PBT
Material hollow bolt	Nickel-plated brass
Material release ring	POM
Material of tubing seal	NBR
Material of tube retaining claw	High alloy steel, non-corrosive