

# Suction grippers ESG-6X20

Part number: 189185

FESTO



Exemplary representation

## Data sheet

Overall data sheet – Individual values depend upon your configuration.

Feature	Value
suction cup size	6x20 mm
Assembly position	Vertical
Design structure	Vacuum connection at top Vacuum connection at side with height compensation with long height compensator
Correlation to suction-cup holder	Size 4
Suction cup shape	Oval, flat
Operating medium	Atmospheric air based on ISO 8573-1:2010 [7:--]
Corrosion resistance classification CRC	1 - Low corrosion stress
Ambient temperature	-10 ... 70 °C
Vacuum connection	M14x1 G1/8 QS-6 PK-4
Materials note	Conforms to RoHS
Material suction cup	NBR