


Suction cup holder ESH-HA-1-PK

Part number: 189194

FESTO

without height compensator, vacuum connection at top, compensator secured by two hexagonal nuts.



Data sheet

Feature	Value
Volume	0.09 cm ³
Assembly position	Vertical
Design structure	Vacuum connection at top
Correlation to suction-cup holder	Size 1
Operating medium	Atmospheric air based on ISO 8573-1:2010 [7:-:-]
Corrosion resistance classification CRC	1 - Low corrosion stress
PWIS conformity	VDMA24364-A1-L
Ambient temperature	-10 ... 60 °C
Product weight	3 g
Mounting type	with lock nut
suction cup mounting	Diameter 3 mm
Vacuum connection	PK-3
Materials note	Conforms to RoHS
Material seals	NBR Steel
Material bracket	Aluminum Nickel-plated brass POM Heat-treatment steel High alloy steel