


Suction cup holder ESH-HB-5-G

Part number: 189211

FESTO

without height compensator, vacuum connection at side.



Data sheet

Feature	Value
Volume	1.921 cm ³
Assembly position	Vertical
Design structure	Vacuum connection at side
Correlation to suction-cup holder	Size 5
Operating medium	Atmospheric air based on ISO 8573-1:2010 [7:-:-]
Corrosion resistance classification CRC	1 - Low corrosion stress
PWIS conformity	VDMA24364-A1-L
Ambient temperature	-10 ... 60 °C
Product weight	91 g
Mounting type	with internal (female) thread
suction cup mounting	M10
Vacuum connection	G1/8
Materials note	Conforms to RoHS
Material bracket	Aluminum Nickel-plated brass POM Heat-treatment steel High alloy steel