


Suction cup holder ESH-HCL-6-G

Part number: 189232

FESTO

with increased height compensator, vacuum connection at top,
compensator secured by two hexagonal nuts.



Data sheet

Feature	Value
Height compensator for suction-cup holder	40 mm
Volume	16.325 cm ³
Assembly position	Vertical
Design structure	Vacuum connection at top with height compensation
Correlation to suction-cup holder	Size 6
Operating medium	Atmospheric air based on ISO 8573-1:2010 [7:-:-]
Corrosion resistance classification CRC	1 - Low corrosion stress
PWIS conformity	VDMA24364-A1-L
Ambient temperature	-10 ... 60 °C
Product weight	560 g
Mounting type	with lock nut
suction cup mounting	M20x2
Vacuum connection	G1/4
Materials note	Conforms to RoHS
Material bracket	Aluminum Nickel-plated brass POM Heat-treatment steel High alloy steel