

Suction cup complete

ESS-20-CN

Part number: 189400

FESTO

easily interchangeable,



Data sheet

| Feature | Value |
|---|---|
| Suction cup height compensator | 7 mm |
| Min. workpiece radius | 50 mm |
| Nominal size | 3 mm |
| suction cup diameter | 20 mm |
| suction cup volume | 2.75 cm ³ |
| Position of connection | on top |
| Assembly position | Any |
| Correlation to suction-cup holder | Size 4 |
| Suction cup shape | Round, bellows, 3.5 convolutions |
| Operating pressure MPa | -95 ... 0 kPa |
| Working pressure | -0.95 ... 0 bar |
| Operating pressure | -13.775 ... 0 psi |
| Nominal operating pressure | -70 kPa |
| Nominal working pressure | -0.7 bar |
| Nominal operating pressure (psi) | -10.15 psi |
| Operating medium | Atmospheric air based on ISO 8573-1:2010 [7:::] |
| Corrosion resistance classification CRC | 1 - Low corrosion stress |
| PWIS conformity | VDMA24364-A1-L |
| Food-safe | See Supplementary material information |
| Ambient temperature | -10 ... 70 °C |
| Retention force at nominal operating pressure | 8.2 N |
| Lateral force at nominal operating pressure | 6.5 N |
| Product weight | 6.9 g |
| Mounting type | Via vacuum port |
| Vacuum connection | M6 |
| Color | Black |
| Shore hardness | 50 +/- 5 |
| Material of threaded plug | Nickel-plated brass Galvanised and chrome-plated steel |
| Materials note | Conforms to RoHS |
| Material suction cup | NBR |