


# Locking threaded plug connector QSK-1/4-5/16-U

Part number: 190713

FESTO

male thread with external hexagon.



## Data sheet

| Feature                                       | Value  |
|---|--|
| Size  | Standard   |
| Nominal size                                  | 4.3 mm   |
| Type of seal on screw-in stud                 | coating  |
| Assembly position                             | Any  |
| Container size                                | 1  |
| Design structure                              | Push/pull principle                                      |
| Operating pressure complete temperature range | -0.95 ... 10 bar   |
| Maritime classification                       | see certificate  |
| Operating medium                              | Compressed air in accordance with ISO8573-1:2010 [7:-:-] |
| Note on operating and pilot medium            | Lubricated operation possible                            |
| Corrosion resistance classification CRC       | 1 - Low corrosion stress                                 |
| Ambient temperature                           | -10 ... 60 °C  |
| Max. tightening torque                        | 14 Nm  |
| Product weight                                | 22.5 g   |
| Pneumatic connection, port 1                  | Male thread 1/4 NPT                                      |
| Pneumatic connection, port 2                  | for tubing, 5/16" outside diameter                       |
| color of release ring                         | Grey   |
| Materials note                                | Conforms to RoHS   |
| Material housing                              | Brass<br>Nickel plated                                   |
| Material release ring                         | POM  |
| Material of tubing seal                       | NBR  |
| Material of tube retaining claw               | High alloy steel, non-corrosive                          |