


Differential pressure valve

LRL-1/8-NPT-QS-5/32-U

Part number: 190904
 Product to be discontinued

FESTO

Without manometer, with male thread and QS plug connector.
 Type to be discontinued. Available until 2023. See Support Portal for alternative products.



Data sheet

Feature	Value
Controller function	Differential pressure, constant
Pneumatic connection, port 1	1/8 NPT
Pneumatic connection, port 2	QS-5/32
Mounting type	Threaded
Supply pressure 1 MPa	0 ... 0.9 MPa
Inlet pressure 1	0 ... 9 bar
Supply pressure 1 psi	0 ... 130.5 psi
Ambient temperature	0 ... 60 °C
Material housing	PBT-reinforced
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:-:-]
Assembly position	Any
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
PWIS conformity	VDMA24364-B1/B2-L
Product weight	19 g
Material of threaded plug	Brass
Materials note	Conforms to RoHS