

Illuminating seal MF-LD-12-24DC

Part number: 19143

FESTO

For MSFG, MSFW Solenoid coil.



Data sheet

Feature	Value
Switching position indicator	LED
Mounting type	On solenoid valve with M3 central screw
Product weight	1.6 g
Electrical connection	Plug pattern type B to EN 175301-803 Rectangular design, MSF
Operating voltage range DC	12 ... 24 V
Protective earth connection	Available
Nominal power, illuminating seal	0.05 W
Protection class	IP65
Ambient temperature	-25 ... 85 °C
PWIS conformity	VDMA24364-B2-L
Material housing	TPE-U(PU)
Color	transparent