

# Illuminating seal MF-LD-230AC

Part number: 19144

FESTO

For MSFG, MSFW Solenoid coil.



## Data sheet

| Feature                                      | Value   |
|--|---|
| Switching position indicator                 | LED   |
| Mounting type                                | On solenoid valve with M3 central screw                         |
| Product weight                               | 1.6 g   |
| Electrical connection                        | Plug pattern type B to EN 175301-803<br>Rectangular design, MSF |
| Nominal operating voltage, AC                | 230 V   |
| Surge strength                               | 4 kV  |
| Protective earth connection                  | Available   |
| Nominal power, illuminating seal             | 0.33 W  |
| Permissible voltage fluctuation              | +/- 10 %  |
| Protection class                             | IP65  |
| Ambient temperature                          | -25 ... 85 °C   |
| CE symbol (see declaration of conformity)    | according to EU low voltage guideline                           |
| UKCA marking (see declaration of conformity) | To UK instructions for electrical equipment                     |
| PWIS conformity                              | VDMA24364-B2-L  |
| Degree of contamination                      | 3   |
| Material housing                             | TPE-U(PU)   |
| Color  | transparent   |