



Lubricator LOE-D-MIDI

Part number: 192576
Classic - do not use for new projects

FESTO

Without threaded connection plates with FRB threaded pin, with metal bowl guard.

Modern alternatives can be found by entering the first four characters of the type code in the search field.



Data sheet

Feature	Value
Size	Midi
Series	D
Assembly position	Vertical +/- 5°
Design structure	proportional standard mist lubricator
Max. oil capacity	110 cm ³
Bowl guard	Metal bowl guard
Working pressure	0 ... 16 bar
Minimum flow rate for lubricator function	8 l/min
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4] Inert gases
Note on operating and pilot medium	Lubricated operation not possible
Corrosion resistance classification CRC	2 - Moderate corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Storage temperature	-10 ... 60 °C
Air purity class at output	Compressed air in accordance with ISO8573-1:2010 [7:4:-] Inert gases
Medium temperature	-10 ... 60 °C
Ambient temperature	-10 ... 60 °C
Product weight	630 g
Mounting type	with accessories
Materials note	Conforms to RoHS
Material bowl	PC