

Rod eye CRSGS-M10X1,25

Part number: 195582

FESTO

For spherical swivelling cylinder mounting on piston rod side per DIN ISO 8139. (Metric series with hex nut per DIN439.)



Data sheet

Feature	Value
Size	M10x1,25
Corrosion resistance classification CRC	3 - High corrosion stress
PWIS conformity	VDMA24364-B2-L
RSBP classification to CD-0033	F5a
Ambient temperature	-40 ... 150 °C
Product weight	87 g
Materials note	Conforms to RoHS
Material of outer ring	High alloy steel
Material housing	High alloy steel
Material of inner ring	High alloy steel
Material nut	High alloy steel