

Spiral plastic tubing PUN-10X1,5-S-1-SW

Part number: 197611

FESTO

Highly flexible, hydrolysis resistant to a great extent



Data sheet

| Feature | Value |
|--|---|
| Working length | 1 m |
| Outside diameter | 10 mm |
| Block length | 0.305 m |
| Inside diameter | 7 mm |
| Coil diameter | 80 mm |
| Number of windings | 9.5 |
| Temperature dependent working pressure | -0.95 ... 10 bar |
| Authorization | TÜV |
| Certificate issuing department | B 013277 0506 00 |
| Operating medium | Compressed air in accordance with ISO8573-1:2010 [7:::] |
| PWIS conformity | VDMA24364-B2-L |
| Ambient temperature | -35 ... 60 °C |
| Product weight | 110 g |
| Pneumatic connection | For push-in connector outside diameter 10 mm |
| Color | Black |
| Shore hardness | D 52 +/-3 |
| Material tubing | TPE-U(PU) |