

DUO spiral plastic tubing PUN-12X2-S-1-DUO-BS

Part number: 197629

FESTO

Highly flexible, hydrolysis resistant to a great extent



Data sheet

Feature	Value
Working length	1 m
Outside diameter	12 mm
Block length	0.44 m
Inside diameter	8 mm
Coil diameter	95 mm
Number of windings	9
Temperature dependent working pressure	-0.95 ... 10 bar
Authorization	TÜV
Certificate issuing department	B 013277 0506 00
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:::]
PWIS conformity	VDMA24364-B2-L
Ambient temperature	-35 ... 60 °C
Product weight	390 g
Pneumatic connection	For push-in connector outside diameter 12 mm
Color	blue/black
Shore hardness	D 52 +/-3
Material tubing	TPE-U(PU)