

DUO spiral plastic tubing PUN-12X2-S-2-DUO-BS

Part number: 197630

FESTO

Highly flexible, hydrolysis resistant to a great extent



Data sheet

Feature	Value
Working length	2 m
Outside diameter	12 mm
Block length	0.704 m
Inside diameter	8 mm
Coil diameter	95 mm
Number of windings	20
Temperature dependent working pressure	-0.95 ... 10 bar
Authorization	TÜV
Certificate issuing department	B 013277 0506 00
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7::-]
PWIS conformity	VDMA24364-B2-L
Ambient temperature	-35 ... 60 °C
Product weight	830 g
Pneumatic connection	For push-in connector outside diameter 12 mm
Color	blue/black
Shore hardness	D 52 +/-3
Material tubing	TPE-U(PU)