


# Axial kit EAMM-A-D32-40P

Part number: 1976465

FESTO



## Data sheet

Feature	Value
Mounting position	Any
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C...60 °C
Relative air humidity	0 - 95 %
Degree of protection	IP40
Ambient temperature	-10 °C...60 °C
Transferable torque	1.6 Nm
Product weight	160 g
Interface code, actuator	D32A D32B
Interface code, motor in	40P
Note on materials	RoHS-compliant