

Spiral plastic tubing

PPS-6-7,5-1/4-BL

Part number: 19796

FESTO

With 2 rotatable fittings and sealing rings, polyamide (not approved for use in the food industry).



Data sheet

Feature	Value
Working length	7.5 m
Outside diameter	7.8 mm
Block length	0.43 m
Inside diameter	6.2 mm
Coil diameter	75 mm
Number of windings	43
Temperature dependent working pressure	-0.95 ... 17.2 bar
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7::-]
Corrosion resistance classification CRC	1 - Low corrosion stress
PWIS conformity	VDMA24364-B2-L
Ambient temperature	-30 ... 80 °C
Nominal tightening torque	11 Nm
Tolerance for nominal tightening torque	± 20 %
Product weight	298 g
Pneumatic connection, port 1	Male thread G1/4
Pneumatic connection, port 2	Male thread G1/4
Color	blue
Material of connecting thread	Brass
Materials note	Conforms to RoHS
Material buckling protection	Steel Galvanized
Material tubing	Polyamide 12