



Flow control valve GRO-1/4

Part number: 2109

FESTO



Data sheet

Feature	Value
Valve function	Throttle function
Pneumatic connection, port 1	G1/4
Pneumatic connection, port 2	G1/4
Adjusting element	Knurled screw
Mounting type	Line installation
Standard nominal flow rate in flow control direction	350 l/min
Working pressure	0 ... 10 bar
Ambient temperature	-20 ... 60 °C
Material housing	Wrought Aluminum alloy
Assembly position	Any
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
PWIS conformity	VDMA24364-B1/B2-L
Medium temperature	-20 ... 60 °C
Product weight	80 g
Materials note	Conforms to RoHS
Material seals	NBR
Material adjusting screw	Steel Galvanized