

# Coupling plug KS4-N-6

Part number: 2152

FESTO

For self-closing quick coupling connectors.



## Data sheet

Feature	Value
Nominal size	4.5 mm
Operating pressure complete temperature range	-0.95 ... 12 bar
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7::-]
Note on operating and pilot medium	Lubricated operation possible
Corrosion resistance classification CRC	1 - Low corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 ... 60 °C
Product weight	15 g
Pneumatic connection, port 1	N-6
Materials note	Conforms to RoHS