

# Metal braided shielded hose

## P-19-SW

Part number: 2235  
Product to be discontinued

FESTO

Type to be discontinued. Available until 2018. See Support Portal for alternative products.



### Data sheet

Feature	Value
Outside diameter	31 mm
Bending radius relevant for flow rate	200 mm
Inside diameter	19 mm
Min. bending radius	60 mm
Operating pressure complete temperature range	-0.95 ... 16 bar
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:::]
Ambient temperature	-20 ... 80 °C
Product weight according to length	0.649 kg/m
Pneumatic connection	für Stecktülle Innen-Ø 19 mm
Color	Black
Shore hardness	A 71 +/- 5
Materials note	Free of copper and PTFE Conforms to RoHS
Materials information for tubing	EPDM SBR