


# Parallel kit EAMM-U-86-D40-80P-102

Part number: 2802441

★ Core product range

Suitable for electric drives.

FESTO



## Data sheet

Feature	Value
Size	86
Assembly position	Any
Gear unit ratio	1:1
Max. speed	5,000 1/min
PWIS conformity	VDMA24364 zone III
Storage temperature	-25 ... 60 °C
Relative air humidity	0 - 95 %
Protection class	IP40
Ambient temperature	-10 ... 60 °C
Mass moment of inertia	175 kgmm <sup>2</sup>
No-load driving torque	0.25 Nm
Transferable torque	9.5 Nm
Product weight	2,300 g
Interface code, actuator	D40B
Interface code, motor in	80P
Materials note	Conforms to RoHS