

Swivel flange CRSNCS-50

Part number: 2895922

FESTO



Data sheet

Feature	Value
Size	50
Based on the standard	ISO 15552 (previously also VDMA 24652, ISO 6431, NF E49 003.1, UNI 10290)
Variants	Excellent corrosion protection
Corrosion resistance classification CRC	4 - Very high corrosion stress
PWIS conformity	VDMA24364-B2-L
RSBP classification to CD-0033	F5a
Ambient temperature	-40 ... 150 °C
Product weight	403 g
Materials note	Conforms to RoHS
Material mounting	High alloy steel, non-corrosive
Material rod end bearing	PTFE Stainless steel
Material screws	High alloy steel, non-corrosive