



Solenoid valve

MZH-3-0,4-K

Part number: 30210

FESTO

Micro Pneumatic, with solenoid coil and manual override, without socket.



Data sheet

Feature	Value
Valve function	3/2 closed, single solenoid
Standard nominal flow rate	4 l/min
Working pressure	0 ... 7 bar
Design structure	Poppet seat
Protection class	IP40 with plug socket
Nominal size	0.4 mm
Type of piloting	direct
Switching time off	4 ms
Switching time on	4 ms
Duty cycle	100%
Characteristic coil data	24V DC: 0,5W
Operating medium	Dried compressed air, lubricated or unlubricated
Medium temperature	-5 ... 50 °C
Ambient temperature	-5 ... 50 °C
Product weight	20 g
Mounting type	with through hole
Pneumatic connection, port 1	Subbase
Pneumatic connection, port 2	Subbase
Pneumatic connection, port 3	Subbase
Materials information for seals	NBR
Materials information, housing	Aluminum die cast