

Plastic tubing

PL-3-BL

Part number: 3453

FESTO

For CK and N connectors (approved for use in the food processing industry).

The maximum pressure value is permissible at the maximum temperature.



Data sheet

Feature	Value
Outside diameter	4.3 mm
Bending radius relevant for flow rate	18 mm
Inside diameter	3 mm
Temperature dependent working pressure	-0.95 ... 9 bar
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:-:-]
Ambient temperature	-30 ... 60 °C
Authorization	TÜV
Product weight according to length	0.0068 kg/m
Color	blue
Shore hardness	D 42 +/-3
Materials note	Free of copper and PTFE Conforms to RoHS
Materials information for tubing	PE