



# Piloted check valve HGL-3/8-NPT

Part number: 34879

FESTO

With sealing ring OL.



## Data sheet

Feature	Value
Valve function	piloted non-return function
Pneumatic connection, port 1	3/8 NPT
Pneumatic connection, port 2	3/8 NPT
Mounting type	Threaded
Standard nominal flow rate	0 ... 900 l/min
Operating pressure MPa	0.02 ... 1 MPa
Working pressure	0.2 ... 10 bar
Pilot pressure MPa	0.12 ... 1 MPa
Pilot pressure	1.2 ... 10 bar 17.4 ... 145 psi
Ambient temperature	-20 ... 80 °C
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
PWIS conformity	VDMA24364-B1/B2-L
Medium temperature	-20 ... 80 °C
Materials note	Conforms to RoHS